



IGENE LABSERVE

Innovative • Interactive • Intuitive

SEED GERMINATION CHAMBER



OPTIONAL TOUCH SCREEN PLC BASED HMI CONTROL SYSTEM

Address: 2/280 11stFloor|Back Side|
Subhash Nagar| New Delhi-110027|
Office: - 011-45002642|
Email: info@igenels.com
www.igenels.com




Seed Germinator is a machine used for germination of different types of seeds in laboratories. These machines are specifically designed growth chambers that create artificial environment using temperature, humidity and light responsible for germination of seeds. These chambers play important role in crop productions.

If needed, we can also customize or further modify these seed germinators with number of accessories including PLC with HMI interface and data logger with USB interface etc.

DESCRIPTION

- ❖ **Chambers:** Our seed germinators are constructed in single chamber and dual chamber designs. Dual chamber machine has two adjacent chambers and each chamber has individual temperature and humidity control system.
- ❖ **Construction:** Inner chamber of each machine is made of thick sheet of stainless steel 304; while the exterior is made of GI sheet which is powder coated for corrosion resistance surface. Each jointed is nicely moulded and arc welded.
- ❖ **Control system:** When using seed germinator accuracy is a prime requirement; therefore, we use powerful PID based temperature and humidity control system supported by high accuracy PT100 RTD sensor and capacitive sensor. In addition, we also use PLC based HMI controller which features colour touch screen, data monitoring and recording and data transfer into computer on user demand. It can be further customized to any level of comfort
- ❖ **Cooling System:** The cooling system in our seed germinator machines are done using branded CFC free and hermetically sealed compressor with R134A refrigerant. It is long life compressor and plays important role in maintaining low temperature.
- ❖ **Humidification:** The humidification system consists of a stainless steel tank and an ISI mark immersion heater. It also features automatic water filling device, when water goes below the low level, this device opens the valve for water re-filling.
- ❖ **Heating:** For heating system, we use tubular air or wire bead heater that are non-corrosive and feature fast heat up.
- ❖ **Air circulation:** In order to achieve uniform temperature and humidity level in every corner of the chamber forced air circulation is needed and in our seed germinators we use high quality motorized blower assembly for this purpose. This assembly not only distributes temperature and humidity uniformly all over the chamber but also offers quiet and vibration free operation for long years.
- ❖ **Illumination:** Good seed growth mostly depends upon sufficient illumination inside the chamber; therefore, we equip our seed germinator machines with high LUX fluorescent LED lights that are controlled through microprocessor controlled cyclic timer. This timer controls the light mode for a week 24 hours a day.





TECHNICAL SPECIFICATIONS

Temperature range	5°C to 60°C
Temperature controller	Digital PID controller
Temperature accuracy	±1%
Temperature sensor	PT-100
Humidity range	50% to 90% RH
Humidity controller	Digital PID controller
Humidity accuracy	±3%
Light	150-170 micromole/m ² /sec
Light timer	24x7 weekly digital timer
Construction	Double walled
Exterior	Mild steel powder coated
Interior	Stainless steel 304
Outer door	Single or double solid doors with lock & key
Inner door	Glass door to view samples
Shelves	3 to 12 (Height adjustable)
Safety	Audio / visual alarm for temperature deviation
Optional	Exterior made of stainless steel 304 / 316 PLC with HMI interface Data logger with USB interface Password protection for controller Caster wheels
Power supply	220 Volts / 50 Hz

Address: 2/280 11stFloor|Back Side|
Subhash Nagar| New Delhi-110027|
Office: - 011-45002642|
Email: info@igenels.com|igenelabserve@gmail.com





IGENE LABSERVE

Innovative • Interactive • Intuitive

STANDARD SIZES / DIMENSIONS

Model	Dimensions (mm)	Volume (Litres)	Volume (Cu. Ft.)
IG-SGC171	505 x 415 x 830	171	6
IG-SGC209	600 x 550 x 910	300	10
IG-SGC340	650 x 580 x 900	340	12
IG-SGC400	700 x 640 x 900	400	14
IG-SGC580	775 x 775 x 970	580	20



Address: 2/280 11stFloor|Back Side|
Subhash Nagar| New Delhi-110027|
Office: - 011-45002642|
Email: info@igenels.com|igenelabserve@gmail.com

